



## **CODE NUMBER**

3082653

#### **DESCRIPTION**

1.5 gpf, XL Sweat Solder Adapter Kit, Polished Chrome Finish, Fixture Connection Top Spud, Single Flush, Regal® Exposed Manual Urinal Flushometer.

#### **DETAILS**

Flush Volume: 1.5 gpf (5.7 Lpf)Finish: Polished Chrome (CP)

• Valve: Diaphragm

• Valve Body Material: Semi-red Brass

• Fixture Type: Urinal

• Fixture Connection: Top Spud

• Rough-In Dimension: 11 ½" (292mm)

Spud Coupling: <sup>3</sup>/<sub>4</sub>" (19mm)
Supply Pipe: <sup>3</sup>/<sub>4</sub>" (19mm)

• Adapter: XL Sweat Solder Adapter Kit (XL)

#### **FEATURES**

- ADA Compliant Metal Oscillating Non-Hold-Open Handle
- Control Stop Plug
- Sweat Solder Adapter with Cover Tube
- Cast Wall Flange with Set Screw
- Vacuum Breaker Flush Connection
- Spud Coupling Wall and Spud Flange for 3/4" Top Spud
- Non-Hold-Open Handle and No External Volume Adjustment to Ensure Water Conservation
- 3/4" I.P.S. Wheel Handle Bak-Chek® Angle Stop



# **COMPLIANCES & CERTIFICATIONS**











(ADA Compliant, BAA Compliant, BABAA Compliant, cUPC Certified, Made in the USA)

#### RECOMMENDED SPECIFICATION

Valve Body, Cover, Tailpiece and Control Stop shall be in conformance with ASTM Alloy Classification for Semi-Red Brass. Valve shall be in compliance with the applicable sections of ASSE 1037 and ANSI/ASME 112.19.2.

## **VALVE OPERATING PRESSURE (FLOWING)**

15-80 PSI (103-552 kPa). Specific fixtures may require greater minimum flowing pressure - consult manufacturer requirements.

# **DOWNLOADS**

- Regal XL Exposed Installation Instructions
- Control Stop Repair and Maintenance Guide
- Flush Connections Flanges Repair and Maintenance Guide
- Tail Piece Repair and Maintenance Guide
- Regal Flushometers Repair and Maintenance Guide
- Flushometer Pressure gauges
- Additional Downloads

### NOTES

All information contained within this document subject to change without notice.

Looking for other variations of the REGAL 186 product? View the general spec sheet with all options.

## WARRANTY

View Warranty Information





REGAL 186-1.5-XL

## **ROUGH-IN**

